

Connecting

Connection Cables


Cables



Technical Data		Type 1681B...
Connection		Fischer 9 pin male – Fischer 9 pin male
Length	m	5/10/20
Diameter	mm	12,3
Degree of protection (EN 60529)		IP65



Technical Data		Type 1685B...
Connection		Fischer 9 pin male – Fischer 9 pin male
Length	m	5/10/sp (max. 20)
Diameter	mm	5,6
Degree of protection (EN 60529)		IP65



Technical Data		Type 1686A...
Connection		Fischer angle 9 pin male – Fischer 9 pin male
Length	m	5/10/sp (max. 20)
Diameter	mm	5,6
Degree of protection (EN 60529)		IP65



Technical Data		Type 1757A...
Connection		Fischer angle 19 pin male – MIL 19 male
Length	m	10/sp (max. 30)
Diameter	mm	5,6
Degree of protection (EN 60529)		IP63



Technical Data		Type 1758A...
Connection		Fischer 19 pin male – D-Sub 37 female
Length	m	10/sp (max. 30)
Diameter	mm	8
Degree of protection (EN 60529)		IP63



Technical Data		Type 1759A...
Connection		Fischer angle 19 pin male – D-Sub 37 female
Length	m	10/sp (max. 30)
Diameter	mm	8
Degree of protection (EN 60529)		IP63



Technical Data		Type 1760A...
Connection		Fischer 19 pin male – MIL 19 male
Length	m	10/sp (max. 30)
Diameter	mm	8
Degree of protection (EN 60529)		IP63



Technical Data		Type 1700A105A...
Connection		Fischer 19 pin male – D-Sub 25 pin male
Length	m	10/sp (max. 30)
Diameter	mm	8
Degree of protection (EN 60529)		IP63

Connecting

Connection Cables

Cables



Technical Data		Type 1700A105B...
Connection		Fischer 19 pin male – D-Sub 25 pin male
Length	m	10/sp
Diameter	mm	8
Degree of protection (EN 60529)		IP63




Technical Data		Type 1700A107A...
Connection		D-Sub 25 pin male – D-Sub 25 pin male
Length	m	10/sp
Diameter	mm	8
Degree of protection (EN 60529)		IP50




Technical Data		Type 1700A109A...
Connection		D-Sub 37 pin male – D-Sub 25 pin male
Length	m	2/sp
Diameter	mm	8
Degree of protection (EN 60529)		IP50



Technical Data		Type 1791A...
Connection		D-Sub 25 pin male – D-Sub 37 pin female
Length	m	10/sp
Diameter	mm	8
Degree of protection (EN 60529)		IP50



Technical Data		Type 1793A...
Connection		D-Sub 25 pin male – MIL 19 male
Length	m	10/sp
Diameter	mm	8
Degree of protection (EN 60529)		IP50



Technical Data		Type 1769A...
Connection		D-Sub 9 pin female – D-Sub 37 pin female D-Sub 12 pin female – D-Sub 37 pin female
Length	m	1/sp
Diameter	mm	6,2/4,9
Degree of protection (EN 60529)		IP50



Technical Data		Type 1779A...
Connection		D-Sub 9 pin female – D-Sub 25 pin male D-Sub 12 pin female – D-Sub 25 pin male
Length	m	2
Diameter	mm	8
Degree of protection (EN 60529)		IP50



Technical Data		Type 5767
Connection		D-Sub 9 pin male – BNC female
Length	m	0,4
Diameter	mm	4,9
Degree of protection (EN 60529)		IP50