

IG-S2 Serie

Berührungsgeber mit Stecker S2 – 2-polig

measure. analyze. innovate.

Maßzeichnung	Sensortyp	Stößelbezeichnung	Bestellnummer
<p>Kabel-Ø 3 mm 1 m lang</p>	IG-4-12/S2	/Standard (ST 37)	6804-12000-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-5-30/S2	/Standard (ST 37)	6805-30000-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-5-30/D/HSS/S2	/D/HSS	6805-30010-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-6-30/S2	/Standard (ST 37)	6806-30000-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-6-30/D/HSS/S2	/D/HSS	6806-30010-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-6-30/I/HSS/S2	/I/HSS	6806-30020-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-M8-30/S2	/Standard (ST 37)	6808-30000-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-M8-30/D/HSS/S2	/D/HSS	6808-30010-2000
<p>Kabel-Ø 4 mm 1 m lang</p>	IG-M8-30/I/HSS/S2	/I/HSS	6808-30020-2000

Stößel gefedert	IG-4-12	IG-5-30	IG-6-30	IG-M8-30
Federkraft	0,5 N	2,5 N	2 N	2 N
Federweg	0,5 mm	2 mm	2 mm	2 mm