

Drawing	Sensor type	Scanning range ¹⁾	Order No.
	RG 1/500	2 – 15 mm	6901-05000-0000
	RG 2/500	20 – 150 mm	6902-05000-0000
	RG 3/500	30 – 250 mm	6903-05000-0000
	RW 1/500	2 – 15 mm	6901-05001-0000
	RW 2/500	15 – 100 mm	6902-05001-0000
	RW 3/500	15 – 125 mm	6903-05001-0000

1) Related to Kodak paper white mat, 200 g/sqm.
Other fiber lengths (250, 750, 1000 mm) on request.

Specifications

Reduction factor for scan range	metal glossy: 1, 2 – 3/rusty: 0.2 – 0.6
Temperature range	-10°C – +250°C

Accessories (more accessories, see last pages)

Article	Order No.
Chopped light amplifier:	
W-R-5-P2	5-pin 2000-00000-0064
W-R-4-P2	4-pin 2000-00000-4064